

## Tiefenschärfe verschiedener Scanner

	DEXIS		Medit		Dentsply Sirona	3Shape	Itero	Shining 3
	Imprevo	IS 3800W	i600	i900	Primescan 1	Trios 5	Lumina	Aoralscan Elite
		IS 3800	i700 i700 wireless		Primescan 2	Trios 6		
Tiefenschärfe	<b>25 mm</b>	18 mm	21 mm	23 mm	20 mm	20 mm	25 mm	22 mm

## Aufnahme Fenster (Capture Zone) der 3 Scannerspitzen (tip)

Standard tip	A (mm)	B (mm)	C (mm)	Capture zone BxC mm <sup>2</sup>
Imprevo	18.5	20	15.6	<b>312</b>
IS 3800W / IS 3800	19	20	16.4	<b>328</b>

Side tip	A (mm)	B (mm)	C (mm)	Capture zone BxC mm <sup>2</sup>
IS 3800W / IS 3800	22.1	17.8	19.7	<b>350.66</b>

Posterior tip	A (mm)	B (mm)	C (mm)	Capture zone BxC mm <sup>2</sup>
IS 3800W / IS 3800	16.6	10.7	14	<b>149.8</b>

